# OSMOSIS, SPEEDY WATER AND DISCOM Demineralization systems

Cominox® expands the concept of safety to all products surrounding steam sterilizers. Technological innovation and quality apply to ancillary products as well, such as Speedy Water and Osmosis demineralizers and Discom water distillers. The global and systematic approach to the areas of hygiene and sterilization are representative of Cominox' philosophical strengths, and demonstrates a profound and conscious attention to detail for all aspects of the medical industry.



# OSMOSIS, demineralizer

- Constant and automatic monitoring of water at two levels (15 and 30 µS/cm)
- · Long-lasting filters (4000 liters)
- · Pressure gauge and booster pump
- · Pressure tank



TECHNOLOGY, STERILIZATION, SAFETY.

# OSMOSIS, SPEEDY WATER AND DISCOM Demineralization systems

### **OSMOSIS**

U.M.		
l/h	7	
bar	from 5 to 7	
bar	from 2 to 6	
mm	400 x 540 x 560	
mm	300	
mm	400	
V - Hz	230 - 50 (single - phase AC)	
W	100	
kg	30	
%	from 96 to 98	
l	4000	
	Vh bar bar mm mm V-Hz W	

Technical data are subject to change without notice

## **SPEEDY WATER**

	U.M.	
Flow rate	l/min	from 0,5 to 0,7
Overall dimensions W x H x D	mm	160 x 540 x180
Operating weight (mass)	kg	5,6
Tap water pressure	bar	from 1 to 4,5
Production capacity	l	300* => 1 year duration**

<sup>\*</sup> Tap water conductivity equal to 650  $\mu$ s/cm \*\* Daily average of 2.5 cycles

Technical data are subject to change without notice

### **DISCOM**

	U.M.	
Distilled water production	l/h	0,57
Capacity	l	4
Overall dimensions Ø x H	mm	200 x 360
Electrical voltage and frequency	V - Hz	230 - 50 (single - phase AC)
Absorbed maximum power	W	580
Weight (mass)	kg	3,5

Technical data are subject to change without notice